

Technical Information

High vapour resistance air and liquid barrier underlay for pitched roofs

Daltex® MultiTX® Plus is a high vapour resistance air & liquid barrier roofing underlay. It is durable, clean, easy to cut & install, and offers excellent temporary protection against wind driven rain, snow & dust. Daltex® MultiTX® Plus conforms to the Construction Products Regulation (EU Regulation No. 305/2011), Underlay for discontinuous roofing (Annex ZA of EN 13859-1) and is manufactured under control of an ISO 9001 quality management system.

TEST	METHOD	MultiTX® Plus						
Product Code		BAB 116						
Mass Per Unit Area (g/m ²)	EN 1849-2	116 (+/- 10)						
Reaction to Fire	EN 11925-2	Class E						
Water Vapour Resistance (Sd)	EN 1931	15 m (+/- 2)						
Water Penetration	EN 1928	Before ageing	Class W1					
		After ageing	Class W1					
Tensile Strength (N/5cm)	EN 12311-1	Before ageing	MD	280	(-70)	CD	170	(-50)
		After ageing	MD	240	(-70)	CD	140	(-50)
Elongation (%)	EN 12311-1	Before ageing	MD	60	(-20)	CD	70	(-20)
		After ageing	MD	40	(-20)	CD	50	(-20)
Tear Resistance (N)	EN 12310-1	MD	140	(-40)	CD	130	(-40)	
Flexibility at low temperature	EN 1109	No cracking at minus 40°C						

Conditions applicable to the end use of the product

Rolls should be stored flat on a clean, level surface and kept under cover. Once the underlay is applied to the roof, the primary roof covering should be installed within one month.

Method of Installation

The membrane should be installed as detailed in national building regulations and relevant agreement certification for this product – see certification logos/numbers below. Any guidelines concerning installation that are supplied with the product should be consulted prior to laying. For general information – the membrane should be unrolled across the roof colour side up, and draped a minimum of 150mm onto the proprietary eaves carrier. The membrane should be fixed to the rafters or boarded sarking, subsequent rows should be lapped by 150mm to shed water out and down the slope. Adjacent rolls should be lapped by 100mm.



Don & Low reserves the right to change specifications or other product information. Don & Low accepts no responsibility or liability for information provided by third parties. No warranties, express or implied, are offered regarding the suitability of any product for your use, as site conditions and customer requirements vary. Should you require further information, please contact us. Products are sold subject to the seller's terms and conditions of sale. No warranty or immunity is offered against infringement of patents or other intellectual property rights.

©Don & Low Limited, 2019. The intellectual property in the products is owned and protected by Don & Low or its licensors.